

TECHSPEC®

75mm Dia. x 100mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#33-921-INK**

10-15 DAYS

[Other Coating Options](#)

-

1

+

A\$572.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| A\$572.00                     |
| Qty 6+                        |
| A\$457.60                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
75.00 ±0.025

Effective Focal Length EFL (mm):  
100.00

|                                                                                |
|--------------------------------------------------------------------------------|
| <b>Focal Length Tolerance (%):</b><br>±1                                       |
| <b>Back Focal Length BFL (mm):</b><br>78.32                                    |
| <b>Focal Length Specification Wavelength (nm):</b><br>587.6                    |
| <b>Clear Aperture CA (mm):</b><br>73.5                                         |
| <b>Centering (arcmin):</b><br><1                                               |
| <b>Center Thickness CT (mm):</b><br>38.70 ±0.20                                |
| <b>Center Thickness CT 1 (mm):</b><br>26.00 ±0.10                              |
| <b>Center Thickness CT 2 (mm):</b><br>12.7 ±0.10                               |
| <b>Radius R<sub>1</sub> (mm):</b><br>66.67                                     |
| <b>Radius R<sub>2</sub> (mm):</b><br>-66.67                                    |
| <b>Radius R<sub>3</sub> (mm):</b><br>-343.59                                   |
| <b>Edge Thickness ET (mm):</b><br>24.66                                        |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BAF10 / N-SF57</a> |
| <b>Surface Quality:</b><br>40-20                                               |
| <b>f/#:</b><br>1.33                                                            |
| <b>Numerical Aperture NA:</b><br>0.38                                          |
| <b>Coating:</b><br>VIS 0° (425-675nm)                                          |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.4% @ 425 - 675nm          |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                          |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                    |
| <b>Bevel:</b><br>Protective bevel as needed                                    |
| <b>Type:</b><br>Achromatic Lens                                                |
| <b>Wavelength Range (nm):</b><br>425 - 675                                     |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |