

TECHSPEC® 75mm Dia. x 150mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#33-925** 3-5 DAYS

[Other Coating Options](#)

- 1 + **A\$580.00**

ADD TO CART

Qty 1-5
A\$580.00
Qty 6+
A\$464.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
75.00 +0.0/-0.025

Effective Focal Length EFL (mm):
150.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 126.46
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 73.5
Centering (arcmin) : <1
Center Thickness CT (mm) : 46.30 ±0.20
Center Thickness CT 1 (mm) : 23.2 ±0.10
Center Thickness CT 2 (mm) : 23.1 ±0.10
Radius R₁ (mm) : 92.05
Radius R₂ (mm) : -72.85
Radius R₃ (mm) : -305.87
Edge Thickness ET (mm) : 36.01
Substrate : ☐ N-BAK1 / N-SF8
Surface Quality : 40-20
f/# : 2.00
Numerical Aperture NA : 0.25
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View