

TECHSPEC[®] 75mm Dia. x 400mm FL, VIS 0° Coated, Achromatic Lens



Stock #88-595 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$556.00

ADD TO CART

Qty 1-5
A\$556.00
Qty 6+
A\$444.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
75.00 +0.0/-0.025

Effective Focal Length EFL (mm):
400.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 392.1
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 73.5
Centering (arcmin) : <1
Center Thickness CT (mm) : 17.05 ±0.20
Center Thickness CT 1 (mm) : 11.05 ±0.10
Center Thickness CT 2 (mm) : 6.00 ±0.10
Radius R₁ (mm) : 246.50
Radius R₂ (mm) : -180.92
Radius R₃ (mm) : -526.7
Edge Thickness ET (mm) : 12.84
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 5.33
Numerical Aperture NA : 0.09
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View