

TECHSPEC[®] 75mm Dia. UV-Enhanced Aluminum Coated, *N*/10 ZERODUR[®] Mirror

See More by [SCHOTT Optical Components](#)



TECHSPEC ZERODUR *N*/10 First Surface Mirrors

Stock **#17-794** **5 In Stock**

-

1

+

A\$848^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	A\$848.00 each
Qty 6-25	A\$681.60 each
Qty 26-49	A\$638.40 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror

Type:

Physical & Mechanical Properties

75.00 +0.00/-0.20

Diameter (mm):

Back Surface:

Commercial Polish	
Protective as needed	Bevel:
90	Clear Aperture (%):
Ground	Edges:
30	Parallelism (arcsec):
7.50 ±0.20	Thickness (mm):

Optical Properties	
λ/10	Surface Flatness (P-V):
ZERODUR®	Substrate: □
20-10	Surface Quality:
R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Coating Specification:
Enhanced Aluminum (250-700nm)	Coating:
Metal	Coating Type:
250 - 700	Wavelength Range (nm):
0.5 J/cm ² @ 355nm, 10ns	Damage Threshold, Reference: □

Material Properties	
0.1	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Precision ZERODUR® Substrates
- λ/10 Flatness
- Low Coefficient of Thermal Expansion

TECHSPEC® ZERODUR® λ/10 First Surface Mirrors are well suited for applications where temperature fluctuation is a concern. The ZERODUR® substrates have a coefficient of thermal expansion (CTE) of ±0.10 x 10⁻⁶/°C, which is an order of magnitude lower than most glass types. The low CTE allows these mirrors to have a consistent reflected wavefront, even when exposed to environments with varying temperature or illumination sources with changing intensity. TECHSPEC® ZERODUR® λ/10 First Surface Mirrors feature precision polished substrates with λ/10 flatness and 20-10 surface quality. Multiple metallic and enhanced metallic coating options are available, allowing for these mirrors to be easily integrated into applications in both the visible and infrared spectrum.

Note: Surface flatness is measured before coating.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).