

TECHSPEC® 75mm Dia. x 100mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#33-924-INK** 10-15 DAYS
[Other Coating Options](#)

- 1 + **A\$596.00**

ADD TO CART

Qty 1-5
A\$596.00
Qty 6+
A\$476.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
75.00 ±0.025

Effective Focal Length EFL (mm):
100.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 78.32
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 73.5
Centering (arcmin) : <1
Center Thickness CT (mm) : 38.70 ±0.20
Center Thickness CT 1 (mm) : 26.00 ±0.10
Center Thickness CT 2 (mm) : 12.7 ±0.10
Radius R₁ (mm) : 66.67
Radius R₂ (mm) : -66.67
Radius R₃ (mm) : -343.59
Edge Thickness ET (mm) : 24.66
Substrate : ☐ N-BAF10 / N-SF57
Surface Quality : 40-20
f/# : 1.33
Numerical Aperture NA : 0.38
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View