

TECHSPEC[®] 75mm Sq., 2mm Thick, Uncoated λ/4 N-BK7 Window



Stock #20-598 3-5 DAYS

-

1

+

A\$224.00

ADD TO CART

Qty 1-5

A\$224.00

Qty 6+

A\$179.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Abbe Number (v_d):
64.17

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):

67.50 x 67.50
Dimensions (mm): 75.00 x 75.00 +0.00/-0.25
Thickness (mm): 2.00 ±0.20
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1 (-30 to +70°C) 8.3 (+20 to +300°C)
Density (g/cm³): 2.51
Edges: Fine Ground
Index of Refraction n_d: 1.516
Knoop Hardness (kg/mm²): 610
Parallelism (arcmin): <1
Poisson's Ratio: 0.206
Substrate: N-BK7
Surface Quality: 60-40
Transmitted Wavefront, P-V: λ/4 (per 50mm Dia.)
Type: Protective Window
Wavelength Range (nm): 350 - 2200
Young's Modulus (GPa): 82
Length (mm): 75.00
Width (mm): 75.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View