

TECHSPEC[®] 75mm Sq., 4mm Thick, VIS-NIR Coated λ/4 N-BK7 Window



Stock #37-072 [CONTACT US](#)

-

1

+

A\$320.00

ADD TO CART

Qty 1-5
A\$320.00
Qty 6+
A\$256.00
Volume Pricing
Request Quote

Get Product Downloads



Abbe Number (v_d):
64.17

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):

67.50 x 67.50
Dimensions (mm): 75.00 x 75.00
Thickness (mm): 4.00 ±0.20
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤ 0.25% @ 880nm R _{avg} ≤ 1.25% @ 400 - 870 nm R _{avg} ≤ 1.25% @ 890 - 1000nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1 (-30 to +70°C) 8.3 (+20 to +300°C)
Density (g/cm³): 2.51
Edges: Fine Ground
Index of Refraction n_d: 1.516
Knoop Hardness (kg/mm²): 610
Parallelism (arcmin): <1
Poisson's Ratio: 0.206
Substrate: N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 400 - 1000
Young's Modulus (GPa): 82
Length (mm): 75.00
Width (mm): 75.00
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant