

TECHSPEC® 76.2 x 272.2mm EFL 30° Bare Gold 100Å Off-Axis Parabolic Mirror



TECHSPEC Gold Off-Axis Parabolic Mirrors

Stock **#35-671** [CONTACT US](#)

[Other Coating Options](#)

- 1 + **A\$1,256.00**

ADD TO CART

Qty 1-5

A\$1,256.00

Qty 6+

A\$1,130.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
76.20 +0.00/-0.38

Effective Focal Length EFL (mm):

272.23
Focal Length Tolerance (%) : ±1
Radius of Curvature (mm) : 508.00
Coating : Bare Gold
Coating Type : Metal
Coating Specification : R _{avg} ≥94% @ 700 - 800nm R _{avg} ≥97% @ 800 - 2,000nm R _{avg} ≥98% @ 2,000 - 12,000nm
Off-Set Angle (°) : 30
Parent Focal Length PFL (mm) : 254.00
Surface Figure, RMS : 3/4λ
Surface Roughness (Angstroms) : <100 RMS
Wavelength Range (nm) : 700 - 12000
Clear Aperture (%) : 90
Surface Quality : 80-50
Compatible Mounting Plates : #63-375
Substrate : Aluminum 6061-T6
Y Offset (mm) : 136.11
Reflected Wavefront, RMS : 3/2λ

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant