

[See all 130 Products in Family](#)

TECHSPEC® 76.2mm Dia. 355nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors



Stock #20-420 **6 In Stock**

⊖ 1 ⊕ **A\$1,288⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-5	A\$1,288.00 each
Qty 6-25	A\$1,160.00 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

<3 **Parallelism (arcmin):**

Clear Aperture (%):

Back Surface:

M10

Diameter (mm):

76.20 +0.00/-0.10

Thickness (mm):

12.70 ±0.20

Optical Properties

Surface Quality:

10-5

Reflection at DWL (%):

99.8

Coating Specification:

R_{abs} >99.8% @ 355nm @ 0-45° AOI

Surface Flatness (P-V):

M10

Coating Type:

Dielectric

Coating:

Laser Mirror (355nm)

Design Wavelength DWL (nm):

355

Angle of Incidence (°):

0-45

Substrate:

[Fused Silica](#) (Corning 7980)

Damage Threshold, By Design:

5.0 J/cm² @ 355nm, 20ns, 20Hz

1MW/cm² @ 355nm

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.

Note: Contact us for customizable wavelengths, sizes, and varying AOI versions.

Compatible Mounts