

76.2mm Dia. 1064nm λ /4 Quartz Waveplate Zero Order



Stock #85-062

3-5 DAYS

-

1

+

A\$3,920.00

ADD TO CART

Qty 1+
A\$3,920.00

Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
46.00

Coating:
Laser V-Coat (1064nm)

Design Wavelength DWL (nm):
1064

Diameter (mm):
76.20 +0.00/-0.25

Substrate:
Crystal Quartz

Retardance: λ/4
Surface Quality: 10-5
Thickness (mm): 10.00 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/8 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0001
Damage Threshold, By Design: □ 3.5 J/cm ² @ 1064nm, 10ns
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View