

TECHSPEC®

76.2mm Silver and VIS 0° Coated, Corner Cube Prism



N-BK7 Corner Cube Retroreflectors with Black Overpaint

Stock **#48-617** 3-5 DAYS

-

1

+

A\$560.00

ADD TO CART

Qty 1+

A\$560.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Beam Deviation (arcsec):
3

Coating:
S1 Silver with protective overcoat (black overpaint) &
S2 VIS 0°

Diameter (mm):
76.20 +0.0/-0.1

Substrate: ☐
[N-BK7](#)

Height (mm): 57.15
Surface Quality: 60-40
Type: Retroreflector
Bevel: Protective bevel as needed
Clear Aperture (%): 95
Height Tolerance (mm): ±0.25
Image Orientation: Left-Handed
Note: Black Overpaint is 30-60µm Thick
Coating Specification: Reflective Surfaces: R _{abs} > 97% FROM 400 - 2500nm @ 0° AOI R _{avg} > 98% FROM 400 - 2500nm @ 0° AOI Entrance: R _{avg} ≤ 0.4% @ 425 - 675nm
Ray Deviation (°): 180
Wavelength Range (nm): 425 - 675
Surface Flatness (P-V): λ/8
Damage Threshold, By Design: ☐ Entrance: 0.5 J/cm ² @ 532nm & 1064nm, 10ns Reflective Surfaces: 5 J/cm2 @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View