

780nm Single Stage Free-Space Optical Isolator



780nm Single Stage Free-Space Optical Isolator, #35-973

Stock **#35-973** 3-5 DAYS

⊖ 1 ⊕ **A\$3,721.60**

ADD TO CART

Qty 1+
A\$3,721.60
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
4.7

Design Wavelength DWL (nm):
780

Minimum Transmission (%):
85

Operating Temperature (°C):
+15 to +40

Transmission (%):
92 (typical)

Type: Single Stage Optical Isolator
Wavelength Range (nm): 750 - 810
Style: Faraday
Damage Threshold, By Design: ☐ 40 W, 4 kW/cm ² @ DVL
Typical Isolation at Design Wavelength (dB): 43
Minimum Isolation at Design Wavelength (dB): 38

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View