

TECHSPEC®

8" Diameter x 40" FL Protected Aluminum, Parabolic Mirror



Stock #32-073-522

3-5 DAYS

-

1

+

A\$1,508.80

ADD TO CART

Qty 1-2
A\$1,508.80
Qty 3+
A\$1,283.20
Volume Pricing
Request Quote

Get Product Downloads

Substrate:

BOROLOAT®

SUPREMAX®

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 8.0 +0.06/-0
Diameter (mm): 203.20 +1.5/-0
Effective Focal Length EFL (inches): 40.0
Effective Focal Length EFL (mm): 1,016.00
Radius of Curvature (mm): 2,032.00
Aperture (f/#): f/5
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 183
Edge Thickness ET (inches): 1.37
Edge Thickness ET (mm): 34.80
Type: Parabolic Mirror
Wavelength Range (μm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference: ☐ 0.3 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant