

TECHSPEC® 8" Diameter x 64" FL Protected Aluminum, Parabolic Mirror



Stock **#32-075-522** [CONTACT US](#)

- 1 + **A\$1,508.80**

ADD TO CART

Qty 1-2
A\$1,508.80
Qty 3+
A\$1,283.20
Volume Pricing
Request Quote

Get Product Downloads

Substrate: [BOROFLOAT®](#)[SUPREMAX®](#)

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 8.0 +0.06/-0
Diameter (mm): 203.20 +1.5/-0
Effective Focal Length EFL (inches): 64.0
Effective Focal Length EFL (mm): 1,625.60
Radius of Curvature (mm): 3,251.20
Aperture (f/#): f/8
Coating: Protected Aluminum (400-2000nm)
Coating Specification: Ravg >85% @400 - 700nm Ravg >90% @400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 183
Edge Thickness ET (inches): 1.37
Edge Thickness ET (mm): 34.80
Type: Parabolic Mirror
Wavelength Range (µm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference: ☐ 0.3 J/cm² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant