

TECHSPEC® 8" Diameter x 80" FL Protected Gold, Parabolic Mirror



Stock #32-076-566 [CONTACT US](#)

- 1 + **A\$1,868.80**

ADD TO CART

Qty 1-2
A\$1,868.80
Qty 3+
A\$1,588.80
Volume Pricing
Request Quote

Get Product Downloads

Substrate: [BOROFLOAT®](#) [SUPREMAX®](#)

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 8.0 +0.06/-0
Diameter (mm): 203.20 +1.5/-0
Effective Focal Length EFL (inches): 80.0
Effective Focal Length EFL (mm): 2,032.00
Radius of Curvature (mm): 4,064.00
Aperture (f/#): f/10
Coating: Protected Gold (700-10000nm)
Coating Specification: R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 183
Edge Thickness ET (inches): 1.37
Edge Thickness ET (mm): 34.80
Type: Parabolic Mirror
Wavelength Range (μm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant