

TECHSPEC[®] 800 - 1200nm, 25mm Dia., Dichroic Shortpass Filter Kit (9 Filters)



Stock **#15-107** [CONTACT US](#)

-

1

+

A\$2,419^{.20}

ADD TO CART

Volume Pricing	
Qty 1+	A\$2,419.20 each
Need More?	Request Quote

Product Downloads

General	
Filters Included :	
Cut-off Wavelengths: 800nm , 850nm , 900nm , 950nm , 1000nm , 1050nm , 1100nm , 1150nm , 1200nm	
Type:	
Shortpass Filter	
Number of Filters:	
9	
Physical & Mechanical Properties	
Diameter (mm):	
25.00	

Physical Durability:
Adhesion per MIL-PRF-13830B, Section C.4.5.12
Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11
Cleaning per MIL-C-48497A Section 4.5.4.2

Environmental & Durability Factors

Environmental Durability:
Humidity per MIL-STD-810H, Section 507.6
Temperature per MIL-STD-810H, Section 501.7 and 502.7

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Sharp Cut-Off Wavelength
- Broad Transmission and Reflection Ranges
- Available in a Range of Common Sizes

Our TECHSPEC® Dichroic Shortpass Filters are designed for a 45° angle of incidence. The rejected light is reflected at 90°, making these filters ideal for use in fluorescence applications or as spectral beamsplitters. The filters feature low polarization dependence, broad spectral ranges, and a precision fused silica substrate. TECHSPEC® Dichroic Shortpass Filters have a sharp cut-off wavelength and are available in a wide range of sizes for ease of system integration. These filters can be combined with TECHSPEC® Dichroic Longpass Filters to create custom bandpass filters.

Note: The chevron on the edge of the filter points towards surface S1 with the primary filter coating on which the light should be incident.

Technical Information

