

8.0mm FL, IR-Cut Filter at 650nm, f/2.5, Micro Video Lens



Stock **#66-892** 3-5 DAYS

[Similar Products](#)



1



A\$94.40

ADD TO CART

Qty 1-49

A\$94.40

Qty 50+

A\$75.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length (mm):
13.50

Filter Thread:
M12 x0.50

Maximum Diameter (mm):
15.0

Maximum Image Circle (mm):

6.00
Horizontal Field of View @ Max Sensor Format: 30.9
Resolution, On-Axis: 80 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 63 lp/mm @ 20% Contrast
Resolution, Full Field: 63 lp/mm @ 20% Contrast
Note: IR Cut-Off Filter Included
Type: M12 Imaging Lens
Focal Length FL (mm): 8.00
Maximum Sensor Format: 1/3"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2.5
Distortion (%): -3.0 @ Full Field
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View