

TECHSPEC® 8.0mm FL f/5.6 Rugged Blue Series M12 Lens



8mm FL Rugged Blue Series M12 Lens



Stock **#36-366** 3-5 DAYS

1

A\$169.00

ADD TO CART

Qty 1+

A\$169.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length (mm):
12.30

Maximum Diameter (mm):
14

Outer Diameter (mm):
14

Weight (g):
3

Horizontal Field of View, 1/3" Sensor: 94.0mm - 34.2°
Maximum Image Circle (mm): 6.00
Numerical Aperture NA, Object Side: 0.0046
Horizontal Field of View @ Max Sensor Format: 94.0mm - 34.2°
Number of Elements (Groups): 5(5)
Wavelength Range (nm): 400 - 700
Type: M12 Imaging Lens
Focal Length FL (mm): 8.00
Primary Magnification PMAG: 0.053X
Maximum Sensor Format: 1/3"
Working Distance (mm): 150 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/5.6
Distortion (%): -3.63 @ Full Field
Back Focal Length BFL (mm): 8.8 - 8.6
Coating Specification: λ/4 MgF ₂ @ 550nm
Entrance Pupil Position (mm): 5.04
Horizontal Field of View, 1/4" Sensor: 69.8mm - 25.7°
Object Space Principal Plane (mm): 8.13
Image Space Principal Plane (mm): 0.94
Field of View at Max Sensor Format: Horizontal: 92.8mm - 34.2° Vertical: 68.9mm - 25.7° Diagonal: 117.5mm - 42.6°
IR Cut Filter: No
Exit Pupil Position (mm): -4.09
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View