

**TECHSPEC® 8mm FL f/2.5, Blue Series M12 Lens**



8mm Blue Series M12 Lens



Stock **#58-203** **20+ In Stock**

⊖ 1 ⊕ **A\$137<sup>00</sup>**

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-49       | <b>A\$137.00</b> each         |
| Qty 50+        | <b>A\$108.00</b> each         |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Blue Series **Product Family:**

M12 Imaging Lens **Type:**

No **IR Cut Filter:**

Imaging Lens Type:  
High Performance M12 Lens

## Physical & Mechanical Properties

Fixed Iris Option:  
12.30 Length (mm):  
14 Maximum Diameter (mm):  
14 Outer Diameter (mm):  
3 Weight (g):

## Optical Properties

Horizontal Field of View @ Max Sensor Format:  
34.2°

Field of View at Max Sensor Format:  
Horizontal: 92.8mm - 34.2°  
Vertical: 68.9mm - 25.7°  
Diagonal: 117.5mm - 42.6°

Horizontal Field of View, 1/3" Sensor:  
94.0mm - 34.2°

Horizontal Field of View, 1/4" Sensor:  
69.8mm - 25.7°

6.00 Maximum Image Circle (mm):

0.0103 Numerical Aperture NA, Object Side:

5(5) Number of Elements (Groups):

400 - 700 Wavelength Range (nm):

8.00 Focal Length FL (mm):

150 - ∞ Working Distance (mm):

f/2.5 Aperture (f/#):

-3.63 @ Full Field Distortion (%):

8.8 - 8.6 Back Focal Length BFL (mm):

M4 MgF<sub>2</sub> @ 550nm Coating Specification:

5.04 Entrance Pupil Position (mm):

8.13 Object Space Principal Plane (mm):

0.94 Image Space Principal Plane (mm):

-3.63 Maximum Distortion (%):

-4.09 Exit Pupil Position (mm):

VIS Lens Wavelength Range:

## Sensor

1/3" Maximum Sensor Format:

1.40 Pixel Size (µm):

## Threading & Mounting

N/A Filter Thread:

S-Mount (M12 x0.5) Mount:

## Regulatory Compliance

Compliant RoHS 2015:

## Product Details

- Up to 1/2", S-Mount Lens
- Up to 5 MegaPixels, 1.4µm Pixel Size Sensors
- High Resolution Board Camera Lens Optimized for Close WD
- 2mm to 35mm Focal Length
- [Ruggedized Designs](#) Also Available


TECHSPEC® Blue Series M12 Lenses feature high resolution performance, along with the same great versatility of our [TECHSPEC® Green Series M12 Lenses](#). Each lens consists of several precision glass elements mounted in a compact, aluminum housing. These lenses can connect to C-Mount cameras using the M12 x 0.5 Adapter for C-Mount Cameras ([#53-675](#)) or the M12 x 0.5 C-Mount Adapter with Rubber O-Ring ([#59-241](#)) for vibration-sensitive environments. TECHSPEC® Blue Series M12 Lenses are ideal for automotive, industrial, and medical imaging application. Prescription data is available by submitting a [Request for Prescription Form](#).

**Note:** Compatible [TECHSPEC® M12 Imaging Lens Accessories](#) available.


Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- Blue Series M12 Lenses: High resolution finite conjugate designs optimized for machine vision working distances.
- [Rugged Blue Series M12 Lenses](#): [Stabilized ruggedization](#) versions of our Blue Series M12 Lenses, utilizing the same optics.
- [Green Series M12 Lenses](#): Finite conjugate designs optimized for machine vision working distances.
- [Red Series M12 Lenses](#): Infinite conjugate designs optimized for high resolution performance out to infinity.
- [HEO Series M12 Lenses](#): Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- [Liquid Lens M12 Lenses](#): Integrated liquid lens for fast electronic focus.


## Technical Information




#58-203, 8mm FL f/2.5, Blue Series M12 Lens, Distortion Plot




#58-203, 8mm FL f/2.5, Blue Series M12 Lens, Relative Illumination Plot




#58-203, 8mm FL f/2.5, Blue Series M12 Lens, Working Distance versus Field of View Plot




#58-203, 8mm FL f/2.5, Blue Series M12 Lens, Modulated Transfer Function (MTF) Plot, 150mm Working Distance, f2.5



#58-203, 8mm FL f/2.5, Blue Series M12 Lens, Depth of Field Plot, 150mm Working Distance, f2.5



#58-203, 8mm FL f/2.5, Blue Series M12 Lens, Modulated Transfer Function (MTF) Plot, 350mm Working Distance, f2.5



#58-203, 8mm FL f/2.5, Blue Series M12 Lens, Depth of Field Plot, 350mm Working Distance, f2.5

| Focal Length | A      | B      | C*          | D      |
|--------------|--------|--------|-------------|--------|
| 2.0mm        | 18.0mm | 21.7mm | 2.26mm      | 4.75mm |
| 3.0mm        | 14.0mm | 17.1mm | 4.8 - 4.7mm | 5.8mm  |
| 4.0mm        | 14.0mm | 19.7mm | 6.1 - 6.0mm | 4.4mm  |
| 5.0mm        | 14.0mm | 14.6mm | 4.0 - 3.9mm | 3.7mm  |
| 6.0mm        | 14.0mm | 14.1mm | 6.9 - 6.8mm | 4.5mm  |
| 8.0mm        | 14.0mm | 12.3mm | 8.8 - 8.6mm | 3.7mm  |
| 10.0mm       | 14.0mm | 17.0mm | 6.6 - 6.3mm | 3.7mm  |

|        |        |        |                |        |
|--------|--------|--------|----------------|--------|
| 12.5mm | 15.0mm | 22.9mm | 10.1 - 9.7mm   | 4.8mm  |
| 17.5mm | 14.0mm | 20.7mm | 5.8 - 4.9mm    | 7.6mm  |
| 25.0mm | 18.0mm | 30.0mm | 8.5 - 6.5mm    | 11.5mm |
| 35.0mm | 18.0mm | 29.5mm | 18.72 - 14.0mm | 14.5mm |



\*Specified for Optimized Working Distance of 150 - 250mm.

;