

TECHSPEC® 8X, 65mm WD CompactTL™ Telecentric Lens



65mm WD, 8X, In-Line Version (Left) and VIS Version (Right)

Stock **#63-744** 3-5 DAYS

⊖ 1 ⊕

A\$526.00

ADD TO CART

Qty 1+

A\$526.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length excluding Threads (mm):
100.00

Horizontal Field of View, 1/2" Sensor:
0.8mm

Horizontal Field of View, 2/3" Sensor:
1.1mm

Filter Thread:
M25.5 x 0.50 (Female) with Required Adapter [#88-212](#)
Sold Separately

Maximum Diameter (mm):

18.00
Weight (g): 53
Horizontal Field of View, 1/3" Sensor: 0.6mm
Numerical Aperture NA, Object Side: 0.088
Working Distance Tolerance (mm): ±1
Number of Elements (Groups): 6 (4)
Note: CompactTL™
Typical Telecentricity @ 588nm (°): 0.06
Typical Distortion @ 588nm (%): 0.1514
Front Thread: M16 x 0.5 (Female)
Manufacturer: Edmund Optics®
Type: Telecentric Lens
Primary Magnification PMAG: 8X
Maximum Sensor Format: 2/3"
Working Distance (mm): 65
Mount: C-Mount
Aperture (f/#): f/45
Coating: N4 MgF ₂
Depth of Field (mm): ±0.03mm (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 1.1 x 0.8
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View