

TECHSPEC[®] 9.0mm Dia. x 25mm FL, VIS 0°, Inked, Plano-Convex Lens



Stock **#38-278-INK** 10-15 DAYS
[Other Coating Options](#)

-

1

+

A\$76.80

ADD TO CART

Qty 1-9

A\$76.80

Qty 10+

A\$69.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
9.00 ±0.025

Effective Focal Length EFL (mm):
25.00 @ 587.6nm

Back Focal Length BFL (mm): 23.68
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.00 ±0.05
Edge Thickness ET (mm): 1.19
Radius R₁ (mm): 12.92
Clear Aperture CA (mm): 8.1
f/#: 2.78
Numerical Aperture NA: 0.18
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View