

[See all 102 Products in Family](#)

TECHSPEC<sup>®</sup> 9.0mm Diameter x 27.0mm FL, 1064nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex(PCX) Lenses



Stock **#65-536** 20+ In Stock

☐ [Other Coating Options](#)

-

1

+

A\$80<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | A\$80.80 each                 |
| Qty 10-25      | A\$72.80 each                 |
| Qty 26-49      | A\$64.80 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

|                      |                           |
|----------------------|---------------------------|
| 9.00 +0.0/-0.025     |                           |
| <1                   | Centering (arcmin):       |
| 2.50 ±0.05           | Center Thickness CT (mm): |
| 1.75                 | Edge Thickness ET (mm):   |
| 8.1                  | Clear Aperture CA (mm):   |
| Protective as needed | Bevel:                    |

|                                    |                                  |
|------------------------------------|----------------------------------|
| Optical Properties                 |                                  |
| 27.00 @ 587.6nm                    | Effective Focal Length EFL (mm): |
| 25.34                              | Back Focal Length BFL (mm):      |
| Laser V-Coat (1064nm)              | Coating:                         |
| R <sub>abs</sub> <0.25% @ 1064nm   | Coating Specification:           |
| N-BK7                              | Substrate: □                     |
| 40-20                              | Surface Quality:                 |
| 1.5λ                               | Power (P-V) @ 632.8nm:           |
| λ/4                                | Irregularity (P-V) @ 632.8nm:    |
| ±1                                 | Focal Length Tolerance (%):      |
| 13.95                              | Radius R <sub>1</sub> (mm):      |
| 3.00                               | f##:                             |
| 0.17                               | Numerical Aperture NA:           |
| 1064                               | Design Wavelength DWL (nm):      |
| 5 J/cm <sup>2</sup> @ 1064nm, 10ns | Damage Threshold, By Design: □   |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| Compliant             | RoHS 2015:                  |
| Compliant             | Reach 219:                  |
| View                  | Certificate of Conformance: |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- <0.25% Reflection at 1064nm for Fiber and Nd:YAG Applications
- BBAR Coating Options Also Available: [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
- [405nm](#), [532nm](#), [633nm](#), [785nm](#), [980nm](#), 1064nm, and [1550nm](#) V-Coated Options Offered

TECHSPEC® 1064nm Laser Line Coated Plano-Convex (PCX) Lenses are designed for maximum throughput at the specified laser wavelength. These lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components. TECHSPEC® 1064nm Laser Line Coated Plano-Convex (PCX) Lenses are available Laser V-Coated in a range of other wavelengths: [405nm](#), [532nm](#), [633nm](#), [785nm](#), [980nm](#), and [1550nm](#). Other coating options are available, including [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#).


LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

Technical Information



Compatible Mounts