

TECHSPEC® 9.0mm Diameter x -12 FL, MgF₂ Coated, Plano-Concave Lens

Stock #48-338 20+ In Stock

 [Other Coating Options](#) A\$64^{.80}**ADD TO CART**

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-9 | A\$64.80 each |
| Qty 10-25 | A\$58.00 each |
| Qty 26-49 | A\$52.00 each |
| Need More? | Request Quote |

Product Downloads

SPECIFICATIONS**General**

Type:

Physical & Mechanical Properties

| | |
|----------------------------------|----------------------|
| Diameter (mm): | 9.00 +0.0/-0.025 |
| Bevel: | Protective as needed |
| Center Thickness CT (mm): | 2.25 |
| Center Thickness Tolerance (mm): | ±0.05 |
| Centering (arcmin): | <1 |
| Clear Aperture CA (mm): | 8.1 |
| Edge Thickness ET (mm): | 3.24 |

Optical Properties

| | |
|---|--|
| Effective Focal Length EFL (mm): | -12.00 |
| Substrate: | <input checked="" type="checkbox"/> N-SP11 |
| f#: | 1.33 |
| Numerical Aperture NA: | 0.38 |
| Coating: | MgF ₂ (400-700nm) |
| Wavelength Range (nm): | 400 - 700 |
| Back Focal Length BFL (mm): | -13.26 |
| Coating Specification: | R _{avg} ≤ 1.75% @ 400 - 700nm |
| Focal Length Specification Wavelength (nm): | 587.6 |
| Focal Length Tolerance (%): | ±1 |
| Radius R ₁ (mm): | -9.42 |
| Surface Quality: | 40-20 |
| Damage Threshold, By Design: | <input checked="" type="checkbox"/> 10 J/cm ² @ 532nm, 10ns |
| Power (P-V) @ 632.8nm: | 1.5λ |
| Irregularity (P-V) @ 632.8nm: | N4 |

Regulatory Compliance

| | |
|-----------------------------|----------------------|
| RoHS 2015: | Compliant |
| Certificate of Conformance: | View |
| Reach 235: | Compliant |

PRODUCT DETAILS


- AR Coated to Provide <1.75% Reflectance per Surface for 400 - 700nm

- Designed for 0° Angle of Incidence


- Various Coating Options: [Uncoated](#), [VIS-EXT](#), [VIS 0°](#), [VIS-NIR](#), [YAG-BBAR](#), [NIR I](#), and [NIR II](#)

TECHSPEC® MgF₂ Coated Plano-Concave (PCV) Lenses are designed to bend parallel input rays to diverge from one another on the output side of the lens causing this lens to have a negative focal length. These lenses can be used for balancing aberrations created by other lenses within a system due to their negative spherical aberration. Plano-Concave (PCV) lenses are commonly used in a variety of applications including image reduction, beam expansion and telescopes. TECHSPEC MgF₂ Coated Plano-Concave (PCV) Lenses are ideal for broadband applications. These lenses are also available [Uncoated](#), [VIS-EXT](#), [VIS 0°](#), [VIS-NIR](#), [YAG-BBAR](#), [NIR I](#), or with [NIR II](#) AR coating options.

TECHNICAL INFORMATION




MgF₂ Coating
 $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$
 Typ. Energy Density Limit: 10 J/cm² @ 532nm, 10ns



N-BK7


Uncoated N-BK7 Typical Transmission



Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV- NIR spectra.

[Click Here to Download Data](#)

N-BK7 with MgF₂ Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with MgF₂ (400-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7)


Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-EXT coating at 0° AOI.




Typical transmission of a 3mm thick N-BK7 window with VIS-EXI (350-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% @ 350 - 700nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:


$$R_{abs} \leq 0.25\% @ 880nm$$

$$R_{avg} \leq 1.25\% @ 400 - 870nm$$

$$R_{avg} \leq 1.25\% @ 890 - 1000nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)




Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.4\% @ 425 - 675nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:


$$R_{abs} \leq 0.25\% @ 532nm$$

$$R_{abs} \leq 0.25\% @ 1064nm$$

$$R_{avg} \leq 1.0\% @ 500 - 1100nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)




Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% @ 600 - 1050nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



COATING CURVES

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS