

TECHSPEC® 950nm CWL, 25mm Dia., Hard Coated OD 4.0 10nm Bandpass Filter



TECHSPEC Hard Coated OD 4.0 10nm Bandpass Filters

Stock #88-572 3-5 DAYS

[Additional Bandwidths](#)

⊖ 1 ⊕ **A\$420.80**

ADD TO CART

Qty 1-5

A\$420.80

Qty 6+

A\$329.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Angle of Incidence (°):
0

Optical Density OD (Average):

≥4.0

Clear Aperture CA (mm):

21.0

Center Wavelength CWL (nm):

950.00 ±2.0

Full Width-Half Max FWHM (nm):

10.00 ±2.0

Full Width-Half Max FWHM Tolerance (nm):

±2.0

Substrate:

Optical Glass

Minimum Transmission (%):

>85

Coating:

Hard Coated

Surface Quality:

80-50

Thickness Tolerance (mm):

±0.1

Type:

Bandpass Filter

Typical Applications:

General Filtering

Blocking Wavelength Range (nm):

200 - 1200

Construction:

Mounted in Black Anodized Ring

Environmental Durability:

Humidity per MIL-STD-810H, Section 507.6
Temperature per MIL-STD-810H, Section 501.7 and 502.7

Physical Durability:

Adhesion per MIL-PRF-13830B, Section C.4.5.12
Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11
Cleaning per MIL-C-48497A Section 4.5.4.2

Mount Thickness (mm):

5.0 ±0.1

Substrate Thickness (mm):

3.5 ±0.5 typical

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

REACH 241:

[Compliant](#)