

[See all 22 Products in Family](#)

9mm Dia. x 4.5mm FL Protected Aluminum, Concave Mirror



Stock #43-674 **20+ In Stock**

- 1 + A\$72.⁸⁰

ADD TO CART

Volume Pricing

Qty 1-49	A\$72.80 each
Qty 50-99	A\$62.40 each
Need More?	Request Quote

Product Downloads

General

Spherical Mirror **Type:**

Physical & Mechanical Properties

±0.5 **Thickness Tolerance (mm):**

9.00 ±0.50 **Diameter (mm):**

90 **Clear Aperture (%):**

Edge Thickness ET (mm):

3.0

Optical Properties

Metal **Coating Type:**

Protected Aluminum (400-2000nm) **Coating:**

400 - 2000 **Wavelength Range (nm):**

4.50 **Effective Focal Length EFL (mm):**

N-BK7 **Substrate:** □

f/0.5 **Aperture (f/#):**

Coating Specification:
R_{avg} >85% @400 - 700nm
R_{avg} >90% @400 - 2000nm

±2 **Focal Length Tolerance (%):**

9.00 **Radius R₁ (mm):**

80-50 **Surface Quality:**

9.00 **Radius of Curvature (mm):**

Regulatory Compliance

Compliant **RoHS 2015:**

Compliant **REACH 201:**

View **Certificate of Conformance:**

Product Details

- Ideal for Focusing Light
- Aluminum and Gold Coating Options
- Available in Sizes Ranging from 9 - 50mm

Concave Spherical Mirrors are ideal for collecting and focusing light in a wide range of applications. These mirrors are available with protected metallic coatings covering the UV, VIS, and IR spectrum. A protective layer increases the coating's durability and prevents corrosion. Concave Spherical Mirrors are available in diameters ranging from 9-50mm for ease of system integration.

Technical Information

