

TECHSPEC[®] 9mm Dia. x 9mm FL, NIR II Coated, Double-Convex Lens



Stock **#67-608-INK** 10-15 DAYS
[Other Coating Options](#)

-

1

+

A\$80.80

ADD TO CART

Qty 1-9
A\$80.80
Qty 10+
A\$72.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
9.00 ±0.025

Back Focal Length BFL (mm):
7.90

Effective Focal Length EFL (mm): 9.00
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-SF5
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <3
Center Thickness CT (mm): 3.45
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.60
Radius R₁=R₂ (mm): 11.38
Clear Aperture CA (mm): 8.10
f#: 1.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 750 - 1550
Damage Threshold, By Design: ☐ 8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View