

[See all 2 Products in Family](#)

BeamR2-Si Scanning Slit Beam Profiler



#24-215 DataRay Scanning Slit Beam Profiler

Stock **#24-215** **1 In Stock**

A\$8,192⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$8,192.00 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Dimensions (mm):
60.96 x 67.31 x 66.17

Dimensional Accuracy:
±1µm

Optical Properties

Spectral Range:
190 - 1150

Beam Diameter (µm):
2µm to 4mm

Sensor

5Hz

Frame Rate:

Electrical

1,000:1

Signal to Noise S/N Ratio (dB):

1 W Total & 0.5 mW/ μm^2

Maximum Power (W):

Threading & Mounting

1/4-20 thread

Mount:

Regulatory Compliance

[Exempt](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Contains SVHC\(s\)](#)

REACH 241:

Product Details

- Designed For Use From 190 to 1150nm
- Measure Beam Diameters of 2 μm to 4mm
- Robust Easy to Use Software Provided

DataRay Scanning Slit Beam Profilers feature a silicon detector making it perfect for a 190 to 1150nm spectral range. Equipped with 2.5 μm slits and larger knife-edge slits, the Beam'R2 is capable of measuring beams with diameters down to 2 μm . Scanning slit instruments offer much higher resolution than camera-based systems, and are compatible with both continuous wave and pulsed laser sources. DataRay Scanning Slit Beam Profilers are ideal for optical assembly and instrument alignment, real-time diagnosis of focusing and alignment errors, real-time setting of multiple assemblies to the same focus. These profilers are USB 2.0 powered and include a 3m USB 2.0 cable.