

Hoya L38 (380nm), 50mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #66-076 CLEARANCE 3-5 DAYS

⊖ 1 ⊕

A\$47.92

ADD TO CART

Qty 1+

A\$47.92

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00

Cut-Off Position λ_c (nm):
380±6

Cut-On Wavelength (nm):
380.00 ±6

Density (g/cm³):
2.96

Glass/Filter Number:

Hoya L38	
Substrate:	Colored Glass
Coating:	Uncoated
Color:	Clear
Surface Quality:	80-50
Transformation Temperature (°C):	480
Thickness (mm):	2.50
Thickness Tolerance (mm):	±0.2
Type:	Longpass Filter
Wavelength:	UV
Dimensional Tolerance (mm):	±0.38
Reflection Factor P _d :	0.91
Bevel:	Protective as needed
Δλ (nm):	<35
TH (%):	>85

Regulatory Compliance

RoHS:	Exempt
Certificate of Conformance:	View