

[See all 14 Products in Family](#)

Adjustable Path Length Transmission Dip Probe Tip, 10-20 mm

See More by [Ocean Optics](#)



Stock #90-577 **NEW** 1 In Stock

⊖ 1 ⊕ A\$692⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | A\$692.80 each |
| Need More? | Request Quote |

Product Downloads

Construction Material:

PEEK

General

Model Number:

RTP-10-20

Optical Properties

Wavelength Range (nm):

200 - 2500

Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Compliant

Reach 250:

Product Details

- Transmission Dip Probes Designed for Reliable In-Solution Absorbance/Transmission Measurements
- Rugged Stainless Steel or PEEK for Tough Process Conditions and Harsh Environments
- Flexible Path Lengths Available with Interchangeable Probe Tips
- Compatible with Ocean Optics Spectrometers and Accessories

Ocean Optics Transmission Dip Probes couple to spectrometers and light sources to measure absorbance and transmission in solutions. Choose from ruggedized high-pressure probe ([#90-569](#)) for demanding process environments or PEEK-jacketed probes ([#90-570](#) and [#90-571](#)) for harsh chemical conditions, spanning UV-Vis to Vis-NIR wavelengths. Easily customize your setup with accessories such as interchangeable probe tips in various path lengths and the protective sleeve ([#90-585](#)) for extended durability in corrosive or high-temperature applications. Ocean Optics Transmission Dip Probes are designed for seamless integration with [Ocean Optics spectroscopy systems and compatible accessories](#).

Technical Information

| Transmission Dip Probe | Transmission Dip Probe Stock Number | Compatible Transmission Dip Probe Tip | Compatible Transmission Dip Probe Tip Stock Number |
|--|-------------------------------------|---|--|
| UV-Vis Heavy-Duty Transmission Dip Probe | #90-569 | Harsh Environment Transmission Dip Probe Tip, 2 mm | #90-582 |
| | | Harsh Environment Transmission Dip Probe Tip, 5 mm | #90-584 |
| | | Harsh Environment Transmission Dip Probe Tip, 10 mm | #90-580 |
| | | Harsh Environment Transmission Dip Probe Tip, 25 mm | #90-581 |
| | | Harsh Environment Transmission Dip Probe Tip, 50 mm | #90-583 |
| UV-Vis Transmission Dip Probe | #90-570 | Stainless Steel Transmission Dip Probe Tip, 2 mm | #90-573 |
| | | Stainless Steel Transmission Dip Probe Tip, 5 mm | #90-576 |
| | | Stainless Steel Transmission Dip Probe Tip, 10 mm | #90-572 |
| | | Adjustable Path Length Transmission Dip Probe Tip, 2–10 mm | #90-578 |
| | | Adjustable Path Length Transmission Dip Probe Tip, 10–20 mm | #90-577 |
| Vis-NIR Transmission Dip Probe | #90-571 | Stainless Steel Transmission Dip Probe Tip, 2 mm | #90-573 |
| | | Stainless Steel Transmission Dip Probe Tip, 5 mm | #90-576 |
| | | Stainless Steel Transmission Dip Probe Tip, 10 mm | #90-572 |
| | | Adjustable Path Length Transmission Dip Probe Tip, 2–10 mm | #90-578 |
| | | Adjustable Path Length Transmission Dip Probe Tip, 10–20 mm | #90-577 |