

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#) / [Allied Vision Manta PoE Cameras](#)

[See all 36 Products in Family](#)

# Allied Vision Manta G-2040C Color CMOS PoE Camera

See More by [Allied Vision](#)



Allied Vision Manta PoE Cameras



Stock **#17-094** [CONTACT US](#)

[Similar Cameras](#)

⊖ 1 ⊕

**A\$4,737.60**

ADD TO CART

Qty 1+

A\$4,737.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Video Output:**  
GigE (PoE)

**Type:**  
Color Camera

**Manufacturer:**  
Allied Vision

|                                                                                            |
|--------------------------------------------------------------------------------------------|
| <b>Mounting Threads:</b><br>¼-20 with Tripod Mount Adapter <a href="#">#89-996</a>         |
| <b>Image Buffer:</b><br>128MB                                                              |
| <b>Camera Family:</b><br>Manta PoE                                                         |
| <b>Model Number:</b><br>Manta G-2040C                                                      |
| <b>Imaging Sensor:</b><br>Sony IMX541                                                      |
| <b>Type of Sensor:</b><br>Progressive Scan CMOS                                            |
| <b>Type of Shutter:</b><br>Global                                                          |
| <b>Camera Sensor Format:</b><br>1.1"                                                       |
| <b>Resolution (MegaPixels):</b><br>20.36                                                   |
| <b>Pixels (H x V):</b><br>4,512 x 4,512                                                    |
| <b>Pixel Size, H x V (µm):</b><br>2.74 x 2.74                                              |
| <b>Sensing Area, H x V (mm):</b><br>12.4 x 12.4                                            |
| <b>Frame Rate (fps):</b><br>5.90                                                           |
| <b>Pixel Depth:</b><br>8/12 bit                                                            |
| <b>Exposure Time:</b><br>Via Software                                                      |
| <b>Connector:</b><br>GigE, RJ45 with Screw Locks                                           |
| <b>Power Supply:</b><br>Power over Ethernet (PoE), via GPIO, or with external power supply |
| <b>Power Consumption (W):</b><br>3.3 (12VDC External Power Supply), 3.9 (PoE)              |
| <b>GPIOs:</b><br>2 opto-isolated inputs, 2 opto-isolated outputs                           |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO) or Software Trigger                     |
| <b>Dimensions (mm):</b><br>71 × 44 × 29 (excludes connectors and lens mount)               |
| <b>Weight (g):</b><br>200                                                                  |
| <b>Mount:</b><br>C-Mount                                                                   |
| <b>Housing:</b><br>Full                                                                    |
| <b>Interface Port Orientation:</b><br>Back Panel                                           |
| <b>Dynamic Range (dB):</b><br>70.8                                                         |
| <b>Operating Temperature (°C):</b><br>+5 to +45                                            |
| <b>Storage Temperature (°C):</b><br>-10 to +70                                             |
| <b>GPIO Connector Type:</b><br>12-pin Hirose (HR10)                                        |
| <b>Machine Vision Standard:</b><br>GigE Vision v1.2, GenICam SFNC V1.2.1                   |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |