

Allied Vision Prosilica GC2450C 2/3" CCD GigE Color Camera

See More by [Allied Vision](#)



Stock **#67-001** [CONTACT US](#)



1



A\$5,414.40

ADD TO CART

Qty 1+
A\$5,414.40

Volume Pricing
Request Quote

Get Product Downloads

Video Output:
GigE

Type:
Color Camera

Manufacturer:
Allied Vision

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#63-432](#)

Image Buffer: 64MB
Note: C-Mount features adjustable back focus
Camera Family: Prosilica GC
Model Number: GC2450C
Imaging Sensor: Sony ICX625
Type of Sensor: Progressive Scan CCD
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 5.00
Pixels (H x V): 2,448 x 2,050
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 8.4 x 7.0
Frame Rate (fps): 15.00
Pixel Depth: 12 bit
Exposure Time: 25µs - 60s
Connector: GigE, RJ45
Power Supply: Power Supply Required and Sold Separately. USA: #15-281 Europe: #15-281 Japan: #15-281 China: #15-281
Power Consumption (W): 3.8 (12VDC External Power Supply)
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 1 non-isolated input, 1 non-isolated output
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 45.7 x 42.9 x 33 (excludes connectors and lens mount)
Weight (g): 106
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -10 to +70
GPIO Connector Type: 12-pin Hirose (HR10)
Machine Vision Standard: GigE Vision v1.2, GenICam SFNC V1.2.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant