

[See all 94 Products in Family](#)

Basler ace2 a2A5328-4gmBAS Monochrome GigE Basic Camera

See More by [Basler](#)



Basler ace2 GigE Cameras (Front)



Stock **#16-603** [CONTACT US](#)

[Similar Cameras](#)

A\$4,224⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$4,224.00 each
Need More?	Request Quote

Product Downloads

Monochrome **Spectrum:**

General

Monochrome Camera **Type:**

a2A5328-4gmBAS **Model Number:**

Basler **Manufacturer:**

ace2 **Camera Series:**

Physical & Mechanical Properties

Dimensions (mm):
55.5 x 29 x 29 (excludes connectors and lens mount)

Weight (g):
<105

Housing:
Full

Sensor

Image Buffer:
Not Specified

Sensor Format:
1.2"

Resolution (Megapixels):
24.40

Frame Rate (fps):
4.00

Pixels (H x V):
5,328 x 4,608

Pixel Size, H x V (µm):
2.74 x 2.74

Sensing Area, H x V (mm):
14.6 x 12.6

Imaging Sensor:
Sony IMX540

Type of Sensor:
Progressive Scan CMOS

Shutter Type:
Global

Pixel Depth:
8/10/12 Bit

Exposure Time:
Freely Programmable

Dynamic Range (dB):
70.7

Machine Vision Standard:
GigE Vision 2.0, GenICam

Electrical

Power Consumption (W):
3.3

Hardware & Interface Connectivity

Interface:
GigE (PoE)

Connector:
GigE, RJ45 with Screw Locks

Power Supply:
Power over Ethernet (PoE) or via GPIO with [#16-644](#)

GPIOs:
1 opto-coupled input line, 2 general purpose I/O (GPIO) lines

Synchronization:
Hardware Trigger (GPIO), Software Trigger, or Free-Run

Interface Port Orientation:
Back Panel

GPIO Connector Type:
6-pin MB

Threading & Mounting

Mount:
C-Mount

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#16-641](#)

Environmental & Durability Factors

Operating Temperature (°C):
-10 to +60

Storage Temperature (°C):
-20 to +80

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 235:**

Product Details

- SONY Pregius S Sensors Available with up to 24MP
- Proven Compact Housing (29 x 29mm)
- Powerful Computer Vision Feature Set with Optional Beyond Features
- [Basler ace GigE Cameras](#) Also Available

Basler ace2 GigE/5GigE Cameras are available in two versions that provide optimized hardware design, proven compact and robust housing, and state of the art CMOS sensor technology with excellent image quality from Sony's 2nd-Gen Pregius, 3rd-Gen STARVIS, or the latest 4th-Gen Pregius S sensors. These second-generation Ace cameras include all of the components of the first-generation Ace cameras along with integrated features such as a status LED, removable IR cut filter, and robust MB connector. The Basler ace2 GigE/5GigE Camera Basic version offers excellent price to performance ratio with powerful Computer Vision feature set, while the Pro version unlocks unique advanced Beyond features such as Pixel Beyond and Compression Beyond for maximum performance to meet with demanding application requirements. These cameras include the industry proven Basler Pylon SDK Software and Driver and conform to GenICam (GigE Vision 2.0) standards, making them a fast and cost-effective solution to software integration. Basler ace2 Cameras are available in both GigE, 5GigE and USB3.0 interfaces and are ideal for a wide range of applications such as factory automation and industrial robotics.

Technical Information



IMX676 Sensor QE Curve



IMX900 Sensor QE Curve



GMAX2505 Sensor QE Curve



IMX546 Sensor QE Curve



IMX545 Sensor QE Curve



GMAX2509 Sensor QE Curve



GMAX2518 Sensor QE Curve



IMX547 Sensor QE Curve



E2525A Sensor QE Curve

;