

[See all 2 Products in Family](#)

## AURORA 40-85eV (15 - 31nm) XUV Phase Retarder

See More by [UltraFast Innovations \(UFI\)](#)



Stock #75-231 **NEW** [CONTACT US](#)

⊖ 1 ⊕ A\$58,752<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	A\$58,752.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

0.85 @ 23.4nm (Fe)  
0.75 @ 18.79 (Ni)

Capacity (PC):

## General

### Note:

Included with the Unit  
9-pin D-Sub connector  
DN40CF window for vacuum chamber integration

## Physical & Mechanical Properties

### Dimensions (mm):

51 x 118

### Clear Aperture CA (mm):

3

## Optical Properties

### Transmission (%):

>25

### Wavelength Range (nm):

14.58 - 30.99

### Extra Beam Path (mm):

3

## Electrical

### Bandwidth (eV):

40 - 85

## Regulatory Compliance

### Certificate of Conformance:

[View](#)

## Product Details

- Near Circular Polarization of Extreme UV (XUV) Light without Adding Dispersion
- Up to 40% Max Transmission
- Spectral Range Options of 40 – 85 eV (15 - 31nm) or 10 – 35 eV (31 - 124nm)

UltraFast Innovations (UFI) Aurora XUV Phase Retarders are designed to act as a quarter waveplate to turn linearly polarized XUV light into circularly polarized light without introducing additional dispersion. These phase retarders achieve close to-circular polarization of PC = 0.75 and feature a > 25% transmission around 66 eV photon energy, at the Ni M2/M3 edge. Broad bandwidth options of 40 – 85eV (15 - 31nm) or 10 – 35eV (31 - 124nm) are available and a clear aperture of 3mm will allow the low divergent XUV light to pass through without clipping. UltraFast Innovations (UFI) Aurora XUV Phase Retarders use a transmission optimized, four mirror-grazing incidence reflection geometry that induces a quarter wave phase offset between the s- and p-polarization components of a linearly polarized input XUV beam. These retarders are ideal for XUV ultrafast high-harmonic, laser-based pump probe, and attosecond applications.

**Note:** Please contact Edmund Optics after placing your order (or prior to ordering) to provide:

- Required cable length between AURORA and the vacuum flange (include units)
- Country of operation / end-use country (required to supply the correct cable type)