

# Coherent® Lasercam™ 33-6859-000 | UV Continuously Variable Attenuator

See More by [Coherent®](#)



Stock #12-419 [CONTACT US](#)

⊖ 1 ⊕ A\$6,400<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$6,400.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

## Physical & Mechanical Properties

Active Area Diameter (mm):  
15

## Optical Properties

Maximum Incident Energy Density (mJ/cm<sup>2</sup>):  
8

Wavelength Range (nm):  
190 - 1100

Min. to Max. Attenuation:  
10000000:1 to 3000:1

## Regulatory Compliance

Compliant

RoHS 2015:

Compliant

Reach 224:

[View](#)


Certificate of Conformance:

## Product Details

- 12 and 14-bit Digital USB 2.0 Interface Options
- High Sensitivity and Dynamic Range
- Intuitive BeamView™ Software Included

The Coherent® Lasercam™ Beam Profiler features excellent signal-to-noise ratio and linear response for accurate pulsed as well as CW laser beam dimension and uniformity measurements. The new BeamView™ 4.4 interface software features TCP/IP control and NI LabVIEW™ library suite, enabling efficient and smooth integration of beam profiling into any application. Examples of analysis functions that can be performed on the acquired beam images include: beam centroid location, beam peak intensity position, pointing stability, total relative power/energy in beam, peak power/energy density of beam, beam divergence, ellipticity, beam intensity uniformity, Gaussian fit, beam diameter/width based on second moments or user selectable percentage of peak/total energy.

## Technical Information



### Intuitive Software Interface

