


BFS-PGE-123S6P-C, Pol. PoE GigE Blackfly® S, Monochrome Camera

See More by [FLIR](#)



FLIR® Blackfly® S PoE GigE Cameras



Stock #22-082 3-5 DAYS



1



A\$7,420.80

ADD TO CART

Qty 1+
A\$7,420.80

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Polarized Monochrome Camera

Manufacturer:

FLIR
Mounting Threads: 1/4-20 with Tripod Mount Adapter #88-210
Image Buffer: 240MB
Camera Family: Blackfly® S
Model Number: BFS-PGE-123S6P-C
Imaging Sensor: Sony IMX253MZR
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1.1"
Resolution (MegaPixels): 12.30
Pixels (H x V): 4,096 x 3,000
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 14.13 x 10.35
Frame Rate (fps): 10.00
Pixel Depth: 10/12 bit
Exposure Time: 36µs to 30s
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power Supply Required and Sold Separately. USA: #88-063 Europe: #88-063 Japan: #88-063 Korea: Not Available China: Not Available
Power Consumption (W): 2.5
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 1 non-isolated bi-directional, 1 non-isolated input
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 29 x 29 x 30 (excludes connectors and lens mount)
Weight (g): 36
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 70.77
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 6-pin Hirose (HR10)
Machine Vision Standard: GigE Vision v1.2

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View

