

[See all 1 Products in Family](#)

Depth of Field Target 5-15



DOF 5-15 Depth of Field Target

Stock **#54-440** **15 In Stock**

-

1

+

A\$1,560⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	A\$1,560.00 each
Qty 5+	A\$1,483.36 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
57.00	Diameter (mm):
57 H x 34 W x 57 D	Dimensions (mm):
Aluminum	Construction:
50.00	Maximum Depth (mm):

Optical Properties

	Substrate:
Black on White-Backed Film	
	Resolution:
5 and 15 lp/mm Scale (both Horizontal and Vertical)	




Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 240:
Compliant	


Product Details



- Test Depth of Field of Your Imaging System
 - Effective Measurement Eliminates the Need for Calculations
- DOF 5-15 Depth of Field Target was developed to standardize an area of optical tolerancing that is most commonly determined theoretically. Optical system design requires stringent depth of field specifications. This target eliminates potentially misleading depth of field calculations. This target solves the problem and very accurately determines the amount of shift an object can undertake before producing an unacceptable image. The definition of what constitutes an acceptable image is determined by the user and the application. The DOF 5-15 Depth of Field Target is made up of two sets of scales. Each, when viewed at 45°, consists of horizontal and vertical lines at a frequency of 5- and 15-line pairs per mm. Instructions included.

Technical Information



Click the image below for an enlarged downloadable file.





Line spread functions of ruling. Taken with VZM™ 200i at 1X PMAG.
Left: Iris Open. Right: Iris Half Open.