

[See all 4 Products in Family](#)

Dual Axis Linear Scale Micrometer on Opal Glass



Stock #58-763 **1 In Stock**

⊖ 1 ⊕ A\$1,248⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-4 | A\$1,248.00 each |
| Qty 5+ | A\$1,186.08 each |
| Need More? | Request Quote |

Product Downloads

General

NIST Certification:
No

Physical & Mechanical Properties

Scale Divisions:
Metric: 25µm
English: 1 mil (0.001")

Dimensions (mm):
25.4 x 76.2

Thickness (mm):

1.50 ±0.100

Dimensional Tolerance (mm):

±0.100

Optical Properties

Chrome on Opal Glass

Substrate:

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 235:

Product Details

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

Technical Information

