

[See all 4 Products in Family](#)

## Dual Axis Linear Scale Micrometer



Stock #58-608 [CONTACT US](#)

A\$1,064<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | A\$1,064.00 each              |
| Qty 5+         | A\$1,011.68 each              |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

#### General

NST Certification:  
No

#### Physical & Mechanical Properties

Scale Divisions:  
Metric: 25µm  
English: 1 mil (0.001")

Dimensions (mm):  
25.4 x 76.2

Thickness (mm):

1.50 ±0.100

**Dimensional Tolerance (mm):**

±0.100

## Optical Properties

Chrome on Glass      **Substrate:**

60-40      **Surface Quality:**

## Regulatory Compliance

**Compliant**      **RoHS 2015:**

[View](#)      **Certificate of Conformance:**

**Compliant**      **Reach 235:**

## Product Details

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

## Technical Information

