

## Dual Bandpass VIS-735nm NIR filter M30.5



Stock #74-566 NEW 1 In Stock

⊖ 1 ⊕ A\$217<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	A\$217.60 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

**Full Width-Half Max FWHM Range (nm):**  
250nm, 50nm ±20 nm

### General

Dual Bandpass Mounted Imaging Filter **Type:**

DB735-30.5 **Model Number:**

### Physical & Mechanical Properties

32.5 **Outer Diameter (mm):**

**Substrate Thickness (mm):**

2mm

## Optical Properties

Color: VIS-735nm-NIR

Surface Quality: 40/20

Transmission (%):  $\geq 90\%$

Transmission Wavelength (nm): 404-645nm, 725-755nm

## Threading & Mounting

Filter Thread: M30.5 x 0.50

Mount Thickness (mm): 5.2

## Regulatory Compliance

Certificate of Conformance: [View](#)

## Product Details

- Block and Transmit Desired Key VIS and NIR Spectral Bands with One Filter
- Remove The Need for Dual Sensor Setups
- Anti-Reflection Coating for Durability and Performance
- Various Mounting Thread Options Available

Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to  $\geq 90\%$  transmission in the visible (VIS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.

**Note:** Other filter threads are available upon request.