

[See all 8 Products in Family](#)

BX-P5G-30C-XC7, Bumblebee® X, IP67 5GigE Stereo Vision Camera

See More by [Teledyne FLIR](#)



Teledyne Imaging FLIR/IIS Bumblebee® X Stereo Vision Cameras - Front



Stock #73-332 **1 In Stock**

- 1 + A\$6,400⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$6,400.00 each
Need More?	Request Quote

Product Downloads

Color	Spectrum:
General	
Color Camera	Type:
BX-P5G-30C-XC7	Model Number:
	Manufacturer:

FLIR

Bumblebee®, IP67

Camera Series:

105
Field of View (°):

Physical & Mechanical Properties

304 x 64 x 38 (excludes connectors and lens mount)
Dimensions (mm):

900
Weight (g):

Full
Housing:

240.00
Baseline Distance (mm):

Optical Properties

3mm (0.3%)
Depth Accuracy (1m) :

15mm (0.75%)
Depth Accuracy (2m):

89mm (1.8%)
Depth Accuracy (3m):

20
Working Distance (m):

Sensor

1/1.8"
Sensor Format:

3.00
Resolution (Megapixels):

20.80
Frame Rate (fps):

3.45 x 3.45
Pixel Size, H x V (µm):

Sony Pregius
Imaging Sensor:

IMX265 CMOS
Type of Sensor:

Global
Shutter Type:

GigE Vision v2.0
Machine Vision Standard:

Electrical

14.5
Power Consumption (W):

Hardware & Interface Connectivity

5GigE (PoE)
Interface:

M12 X-coded 8-pin for Ethernet, 12-pin GPIO
Connector:

Power over Ethernet (PoE) or via GPIO with 10-24V Power Supply
Power Supply:

1 opto-isolated input, 1 opto-isolated output, 4 non-isolated input
GPIOs:

Hardware Trigger (GPIO) or Software Trigger
Synchronization:

Back Panel
Interface Port Orientation:

12-pin Hirose (HR10)
GPIO Connector Type:

Threading & Mounting

1/4-20, M4
Mounting Threads:

Environmental & Durability Factors

-10 to +50
Operating Temperature (°C):

-30 to +60
Storage Temperature (°C):

[View](#)

Product Details

- High Accuracy Depth Sensing
- Low Latency and Wide Baseline Distance for Real-Time Applications
- IP67 Industrial Rated
- Onboard Processing
- Comprehensive [SDK](#) Available

Teledyne Imaging FLIR/IIS Bumblebee® X Stereo Vision Cameras are IP67 rated color stereo cameras that are factory calibrated to a 240mm baseline distance with 3-megapixel (MP) sensors for high accuracy. These cameras feature onboard processing and, combined with the comprehensive Spinnaker® 3D SDK, can output depth maps and color data for point cloud conversion and colorization. Designed for superior depth accuracy across a broad working distance of 0.5m to 20m, these cameras are available with a variety of Field-of-View options. Teledyne Imaging FLIR/IIS Bumblebee® X Stereo Vision Cameras are available in a 5Gige interface and feature a Sony Pregius 1/1.8" sensor with 3.45µm pixels. The low latency of these cameras makes them ideal for real-time applications, including warehouse automation, autonomous mobile robot (AMR), automated guided vehicle (AGV), pick & place, bin picking, and palletization applications.

Bumblebee X is currently supported under Windows and Linux (Desktop and ARM processors) using Spinnaker SDK (Version 4.2+). Under this software release, customers can stream the two raw images, rectified images, as well as the camera generated disparity images. Image feeds and camera settings are accessible using our familiar SpinView GUI application. A ROS2 plugin is also provided.

;