


TECHSPEC[®] Elliptical Mirror, 12.7mm Minor Axis, 750 - 1100nm



Stock #72-951 12 In Stock

-

1

+

A\$177^{.60}

ADD TO CART

Volume Pricing	
Qty 1-5	A\$177.60 each
Qty 6+	A\$142.40 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror

Type:

Flatness specification is Peak to Valley

Note:

Physical & Mechanical Properties

±0.020

Thickness Tolerance (inches):

3.81 ±0.51

Thickness (mm):

Clear Aperture CA (mm): 11.43 (Minor Axis) 16.15 (Major Axis)	
Dimensional Tolerance (inches): ±0.015	
Dimensional Tolerance (mm): ±0.38	
Major Axis (mm): 17.96	
Minor Axis (mm): 12.70	
Optical Properties	
Coating Type: Dielectric	
Coating: Dielectric Mirror (750-1100nm)	
Surface Flatness (P-V): λ/8	
Wavelength Range (nm): 750 - 1100	
Substrate: ☐ BOROFLOAT®	
Coating Specification: R _{avg} >98% @ 750 - 1100nm (0 - 45°) R _{avg} >99% @ 750 - 1100nm (0°)	
Surface Quality: 60-40	
Damage Threshold, By Design: ☐ 1 J/cm² @ 1064nm, 20ns, 20Hz	
Regulatory Compliance	
Certificate of Conformance: View	

Product Details

- Circular Profile When Oriented at 45°
- Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
- Enhanced Reflectivity and LIDT over Metallic Coatings

TECHSPEC® Broadband Dielectric Elliptical Flat Mirrors are ideal for research and astronomical applications. Because of their elongated major axis, they are suited to bending and folding light at precise angles with minimum wavefront distortion. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. TECHSPEC® Broadband Dielectric Elliptical Flat Mirrors feature a BOROFLOAT® substrate and are available with minor axes up to 76.20mm and major axes up to 107.77mm