

[See all 16 Products in Family](#)

# CM3-U3-13Y3C-S-BD 1/2" Chameleon®3 Color Camera

See More by [Teledyne FLIR](#)



USB 3.0 FLIR Chameleon Camera



Stock **#70-323** **2 In Stock**

⊖ 1 ⊕ **A\$664<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>A\$664.00</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

Color **Spectrum:**

**General**

Color Camera **Type:**

CM3-U3-13Y3C-S-BD **Model Number:**

**Manufacturer:**

FLIR

Camera Series:

Chameleon<sup>®</sup>3

## Physical & Mechanical Properties

Dimensions (mm):

40 × 31 (board level)

Weight (g):

27.9

Housing:

Board Level

## Sensor

Image Buffer:

16MB

Sensor Format:

1/2"

Resolution (Megapixels):

1.30

Frame Rate (fps):

149.00

Pixels (H x V):

1,280 x 1,024

Pixel Size, H x V (µm):

4.8 x 4.8

Sensing Area, H x V (mm):

6.14 x 4.92

Imaging Sensor:

ON Semi PYTHON 1300

Type of Sensor:

Progressive Scan CMOS

Shutter Type:

Global

Pixel Depth:

10 bit

Exposure Time:

10µs - 1s

Dynamic Range (dB):

56.19

Machine Vision Standard:

USB3 Vision v1.0

## Hardware & Interface Connectivity

Interface:

USB 3.0

Connector:

USB 3.1 Gen 1, Micro-B with Screw Locks

Power Supply:

Power over USB or via GPIO

GPIOs:

1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports

Synchronization:

Hardware Trigger (GPIO)

Interface Port Orientation:

Side Panel

GPIO Connector Type:

9-pin JST

## Threading & Mounting

Mount:

S-Mount (M12 x 0.5)

Mounting Threads:

¼-20 with Tripod Mount Adapter #88-210

## Environmental & Durability Factors

Operating Temperature (°C):

0 to +45

Storage Temperature (°C):

-30 to +60

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- USB3 Connectivity
- Lightweight Construction
- Compact Design



Teledyne  
Authorized  
Distributor

### Teledyne FLIR IIS Chameleon®3: Easy integration with USB3

Compact USB3 cameras

The **Chameleon®3** camera line combines popular CCD and CMOS image sensors with the ease of use of USB 3.0, with a compact form factor and camera sensor resolutions ranging from 1.3 MP to 5.0 MP.

These cameras feature a compact 44 x 35 x 19.5mm lightweight metal case designed for reliability. They offer multiple mounting points and a locking USB 3.0 connection. The camera includes an on-camera frame buffer for image retransmission and an optoisolated GPIO with a locking connection.

#### Features

- Compact form factor
- On-camera image processing: color interpolation, gamma, & LUT
- Data interface: USB3
- 16 MByte frame buffer
- LED Status indicator
- Spinnaker SDK and FlyCapture interfaces

#### Applications

- Life science instrumentation
- Factory automation
- Biometrics kiosk solutions
- Ophthalmoscopy
- 3D scanning
- Automated optical inspection