

Coherent® PowerMax USB PM10-19C Measurement System 1168344 | 10W

See More by [Coherent®](#)



Stock #12-409 **6 In Stock**

⊖ 1 ⊕ A\$2,568⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	A\$2,568.00 each
Need More?	Request Quote

Product Downloads

General

Model Number:
PM10-19C
Coherent Part Number: 1168344

Type:
Meterless

Calibration Uncertainty (%):
±2

Long Pulse Joule Mode Range (J):

0.5 - 10

Cooling Method:
Water/Air (intermittent)

Maximum Incident Energy Density (J/cm²):
0.6 @ 1064nm, 10ns

Physical & Mechanical Properties

Active Area Diameter (mm):
19

Optical Properties

Calibration Wavelength (nm):
10600

Wavelength Range (nm):
190 - 11000

Wavelength Range (μm):
0.19 - 11

Sensor

Type of Sensor:
Thermopile

Electrical

Spectral Compensation Accuracy (%):
±1.5

Maximum Intermittent Power, <5min (W):
30 (air-cooled)

Maximum Incident Power Density (kW/cm²):
6

Power Range:
10mW - 10W

Hardware & Interface Connectivity

Length of Cable (m):
2.5

Computer Interface:
USB

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Reach 224:
[Contains SVHC\(s\)](#)

Certificate of Conformance:
[View](#)

Product Details

- Superior Damage Resistance
- Wide Dynamic Range
- ISO 17025 Certified

Coherent® Thermopile Power Sensors are ideal for measuring the average power of continuous wave lasers or pulsed laser energy. Thermopile sensors operate by absorbing and converting incident laser radiation into heat, which then flows to a heat sink. The temperature difference between the absorber and heat sink is converted into an electrical signal by a thermocouple junction. Coherent® Thermopile Power Sensors, unlike semiconductor sensors, do not saturate. Unlike semiconductor sensors, thermopile sensors feature high power capability and flat spectral response.