

[See all 10 Products in Family](#)

# Coherent® Thermopile Power Sensor 1098498 | 100mW - 30W, UV Coating, DB25

See More by [Coherent®](#)



Stock #12-406 [CONTACT US](#)

− 1 + A\$2,392<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	A\$2,392.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Model Number:**  
PM80X  
Coherent Part Number: 1098498

**Type:**  
Meterless

**Calibration Uncertainty (%):**  
±1

**Long Pulse Joule Mode Range (J):**

0.5 - 50

Cooling Method:

Air

Maximum Incident Energy Density (J/cm<sup>2</sup>):

0.6 @ 1064nm, 10ns

## Physical & Mechanical Properties

Active Area Diameter (mm):

19

## Optical Properties

Resolution:

10mW

Calibration Wavelength (nm):

514

Wavelength Range (nm):

150 - 1000

Wavelength Range (μm):

0.15 - 1

## Sensor

Type of Sensor:

Thermopile

## Electrical

Maximum Intermittent Power, <5min (W):

50 (air-cooled)

Maximum Incident Power Density (kW/cm<sup>2</sup>):

6

Power Range:

100mW - 30W

## Hardware & Interface Connectivity

Length of Cable (m):

2.0

Computer Interface:

DB25

## Regulatory Compliance

RoHS 2015:

[Exempt](#)

Reach 224:

[Contains SVHC\(s\)](#)

Certificate of Conformance:

[View](#)

## Product Details

- Superior Damage Resistance
- Wide Dynamic Range
- ISO 17025 Certified

Coherent® Thermopile Power Sensors are ideal for measuring the average power of continuous wave lasers or pulsed laser energy. Thermopile sensors operate by absorbing and converting incident laser radiation into heat, which then flows to a heat sink. The temperature difference between the absorber and heat sink is converted into an electrical signal by a thermocouple junction. Coherent® Thermopile Power Sensors, unlike semiconductor sensors, do not saturate. Unlike semiconductor sensors, thermopile sensors feature high power capability and flat spectral response.