

TECHSPEC® f/2.5, Visible, 8.0mm HEO Series M12 Lens



8.0mm Focal Length

Stock #63-759 **9 In Stock**

⊖ 1 ⊕ A\$231⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-49 | A\$231.00 each |
| Qty 50+ | A\$182.00 each |
| Need More? | Request Quote |

Product Downloads

General

HEO Series **Product Family:**

M12 Imaging Lens **Type:**

No **IR Cut Filter:**

Meets IEC IPX7 and IPX9K **Imaging Lens Type:**

Physical & Mechanical Properties

| | |
|-------|-------------------------------|
| Fixed | Iris Option: |
| 15.00 | Length (mm): |
| 14 | Maximum Diameter (mm): |
| 14 | Outer Diameter (mm): |
| 4 | Weight (g): |

Optical Properties

Horizontal Field of View @ Max Sensor Format:
390.7mm - 51.9°

Field of View at Max Sensor Format:
Horizontal: 390.7mm - 51.9°
Vertical: 249.7mm - 34.5°
Diagonal: 442.8mm - 57.8°

Horizontal Field of View, 1/1.7" Sensor:
390.7mm - 51.9°

Horizontal Field of View, 1/2" Sensor:
341.7mm - 46.1°

Horizontal Field of View, 1/2.5" Sensor:
306.3mm - 41.8°

Horizontal Field of View, 1/3" Sensor:
249.6mm - 34.5°

Horizontal Field of View, 1/4" Sensor:
184.6mm - 25.9°

Maximum Image Circle (mm):
10.00

Numerical Aperture NA, Object Side:
0.0039

Resolution, On-Axis:
145 lp/mm @ 20% Contrast

Number of Elements (Groups):
6 (5)

Wavelength Range (nm):
425 - 675

Focal Length FL (mm):
8.00

Working Distance (mm):
400 - ∞

Aperture (f/#):
f/2.5

Distortion (%):
-9.15 @ Full Field

Back Focal Length BFL (mm):
8.67 - 8.53

Coating Specification:
425 - 625nm BBAR

Entrance Pupil Position (mm):
3.67

Object Space Principal Plane (mm):
7.82

Image Space Principal Plane (mm):
0.97

Maximum Distortion (%):
-9.15

Exit Pupil Position (mm):
-7.65

Lens Wavelength Range:
VIS

Sensor

Maximum Sensor Format:
1/1.7"

Pixel Size (µm):
5.00

Threading & Mounting

Filter Thread:
N/A

Mount:

Environmental & Durability Factors

Environmental Rating:
IPX7 and IPX9K

Type of Ruggedization:
Waterproof (IPX7 and IPX9K)

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

REACH 241:
Compliant

Product Details

- Up to 1/2", S-Mount Lens
- Up to 1.2 MegaPixels, 5µm Pixel Size Sensors
- Meets IEC Ingress Protection Ratings of IPX7 and IPX9K
- 2.2mm to 8mm Focal Length


TECHSPEC® HEO Series M12 Lenses integrate high performance optics into a sealed, ruggedized enclosure. Designed to meet IEC Ingress Protection Codes IPX7 and IPX9K, these lenses withstand exposure to water up to 1 meter depth for 30 minutes and operate in close-range high-pressure, high-temperature water spray downs. Threaded for M12 x0.5, these lenses are optimized for 1/3" and 1/2" sensor formats. Each HEO Series Lens is waterproof, dustproof, and fog proof with the ability to be hermetically sealed to a camera. TECHSPEC® HEO Series M12 Lenses are ideal for harsh environment applications, such as automotive. Prescription data is available by submitting a [Request for Prescription Form](#)

Note: Compatible [TECHSPEC® M12 Imaging Lens Accessories](#) available.


Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- **Blue Series M12 Lenses:** High resolution finite conjugate designs optimized for machine vision working distances.
- **Rugged Blue Series M12 Lenses:** Stabilized ruggedization versions of our Blue Series M12 Lenses, utilizing the same optics.
- **Green Series M12 Lenses:** Finite conjugate designs optimized for machine vision working distances.
- **Red Series M12 Lenses:** Infinite conjugate designs optimized for high resolution performance out to infinity.
- **HEO Series M12 Lenses:** Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- **Liquid Lens M12 Lenses:** Integrated liquid lens for fast electronic focus.


Technical Information




#63-759, f/2.5, Visible, 8.0mm HEO Series M12 Lens, Distortion Plot




#63-759, f/2.5, Visible, 8.0mm HEO Series M12 Lens, Relative Illumination Plot




#63-759, f/2.5, Visible, 8.0mm HEO Series M12 Lens, Working Distance versus Field of View Plot




#63-759, f/2.5, Visible, 8.0mm HEO Series M12 Lens, Modulated Transfer Function (MTF) Plot, 400mm Working Distance, f2.5



#63-759, f/2.5, Visible, 8.0mm HEO Series M12 Lens, Depth of Field Plot, 400mm Working Distance, f2.5



#63-759, f/2.5, Visible, 8.0mm HEO Series M12 Lens, Modulated Transfer Function (MTF) Plot, 8000mm Working Distance, f2.5



#63-759, f/2.5, Visible, 8.0mm HEO Series M12 Lens, Depth of Field Plot, 8000mm Working Distance, f2.5

| Focal Length | A | B | C | D |
|--------------|--------|--------|-------|-------|
| 2.2mm | 21.0mm | 16.4mm | 2.2mm | 5.4mm |
| 3.6mm | 14.0mm | 14.1mm | 4.5mm | 4.5mm |
| 8.0mm | 14.0mm | 15.0mm | 8.7mm | 4.0mm |

