


Concentric Circles Reticle, 1.2 - 18mm Dia, 1.2mm Increments

See More by [Mitutoyo](#)



#56-007: Concentric Circles Reticle, 1.2 - 18mm Dia, 1.2mm Increments

Stock **#56-007** 3 In Stock

-

1

+

A\$257^{.60}

ADD TO CART

Volume Pricing	
Qty 1+	A\$257.60 each
Need More?	Request Quote

Product Downloads

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Utilizes Mtutoyo [Infinity Corrected Objectives](#)
- Trinocular Design Allows for Easy Video Adaptation
- Turret Accepts up to Four Objectives
- Objectives and Light Source Sold Separately

Designed to yield high magnifications at long working distances, the Mtutoyo FS70 Inspection Microscope is an ideal choice for many inspection and quality assurance applications. Incorporating Mtutoyo's full line of visible [infinity-corrected objectives](#), the microscope system obtains magnifications from 20X– 8000X and working distances from 6 – 34mm. The focusing eyepieces can accept 25mm diameter reticles. The 50/50 trinocular head features 50mm of coarse movement, 0.1mm/rev of fine movement, and simultaneous video and binocular viewing.

Note: [Objectives](#) and [illumination](#) are sold separately.

Technical Information

Microscope System	
Mtutoyo FS70 Microscope System (includes #55-999, #56-000, #56-001, #56-002)	#56-003
Microscope Head (One Required)	
Mtutoyo FS70 Microscope Head	#55-999
Microscope Stand (One Required)	
Mtutoyo FS70 Microscope Stand	#56-000
Microscope Eyepieces in Pairs (One Required)	
10X WF Focusing Eyepieces, 24mm Field Dia.	#56-001
15X WF Focusing Eyepieces, 16mm Field Dia.	#56-310
20X WF Focusing Eyepieces, 12mm Field Dia.	#56-004
Microscope Turret (One Required)	
Manual 4 Position Turret for Mtutoyo FS70	#56-002
Motorized 4 Position Turret for Mtutoyo FS70	#56-313
Microscope Stage (Optional)	
2" x 2" XY-Axes Positioning Stage	#56-011
Accessories and Reticles (Optional)	
Fiber Optic Light Guide for FS70, 72" Length	#56-008
Polarizer Set	#56-009
C-Mount Coupler (1X) for Video Adaptation	#56-010
90° Crossline, Reticle	#56-005
Concentric Circles Reticle, 1.2 - 18mm Dia, 1.2mm Increments	#56-007
20mm Line/0.1mm Divisions, Reticle	#56-183
5mm Line/0.05mm Divisions, Reticle	#56-184
90°/60° Crossline, Reticle	#56-311

Stock No.	Objective	WD (mm)	Resolving Power (μm)	10X Eyepiece #56-001		15X Eyepiece #56-310		20X Eyepiece #56-004	
				Mag.	FOV (mm)	Mag.	FOV (mm)	Mag.	FOV (mm)
#58-235	MPlan Apo 1X	11	11	10-20X	24-12	15-30X	16-8	20-40X	12-6
#46-142	MPlan Apo 2X	34	5	20-40X	12-6	30-60X	8-4	40-80X	6-3
#46-143	MPlan Apo 5X	34	2	50-100X	4.8-2.4	75-150X	3.2-1.6	100-200X	2.4-1.2
#66-383	MPlan Apo 7.5X	35	1.3	75-150X	3.2-1.6	112.5-225X	2.13-1.07	150-300X	1.6-0.8
#46-144	MPlan Apo 10X	33.5	1	100-200X	2.4-1.2	150-300X	1.6-0.8	200-400X	1.2-0.6
#46-145	MPlan Apo 20X	20	0.7	200-400X	1.2-0.6	300-600X	0.8-0.4	400-800X	0.6-0.3
#46-146	MPlan Apo 50X	13	0.5	500-1000X	0.48-0.24	750-1500X	0.32-0.16	1000-2000X	0.24-0.12
#46-147	MPlan Apo 100X	6	0.4	1000-2000X	0.24-0.12	1500-3000X	0.16-0.08	2000-4000X	0.12-0.06
#46-398	MPlan Apo 20X SL	30.5	1	200-400X	1.2-0.6	300-600X	0.8-0.4	400-800X	0.6-0.3
#46-399	MPlan Apo 50X SL	20.5	0.7	500-1000X	0.48-0.24	750-1500X	0.32-0.16	1000-2000X	0.24-0.12
#46-401	MPlan Apo 100XSL	13	0.5	1000-2000X	0.24-0.12	1500-3000X	0.16-0.08	2000-4000X	0.12-0.06
#34-247	MPlan Apo 5X HR	25.5	1.3	50-100X	4.8-2.4	75-150X	3.2-1.6	100-200X	2.4-1.2
#58-236	MPlan Apo 10X HR	15	0.6	100-200X	2.4-1.2	150-300X	1.6-0.8	200-400X	1.2-0.6
#58-237	MPlan Apo 50X HR	5.2	0.3	500-1000X	0.48-0.24	750-1500X	0.32-0.16	1000-2000X	0.24-0.12
#58-238	MPlan Apo 100XHR	1.3	0.3	1000-2000X	0.24-0.12	1500-3000X	0.16-0.08	2000-4000X	0.12-0.06