


Fly's Eye Array 10 x 10mm, 400μm Pitch, 6° Divergence



Microlens Arrays



Stock #12-845 3-5 DAYS



1



A\$1,128.00

ADD TO CART

Qty 1-10
A\$1,128.00
Qty 11+
A\$992.00
Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
1.53

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating:

Uncoated
Type: Fly's Eye Lens Array
Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.05
Dimensions (mm): 10.0 x 10.0
Divergence Angle (°): ±6
Lens Profile: Spherical
Pitch (µm): 400.00
Pitch Tolerance (µm): ±0.25
Radius R (mm): 0.70
Thickness (mm): 2.25
Thickness Tolerance (mm): ±0.05
Type of Optics: Double-Convex

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View