

## Dual Bandpass VIS-850nm NIR filter M37



Stock #74-577 **NEW** [CONTACT US](#)

- 1 + **A\$254<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>A\$254.40</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

**Full Width-Half Max FWHM Range (nm):**  
250nm, 50nm ±20 nm VIS, ±10 nm NIR

### General

Dual Bandpass Mounted Imaging Filter **Type:**

DB850-37 **Model Number:**

### Physical & Mechanical Properties

39 **Outer Diameter (mm):**

**Substrate Thickness (mm):**

2mm

## Optical Properties

Color:  
VIS-850nm-NIR

Surface Quality:  
40/20

Transmission (%):  
≥90%

Transmission Wavelength (nm):  
404-645nm, 835-875nm

## Threading & Mounting

Filter Thread:  
M37 x 0.75

Mount Thickness (mm):  
5.2

## Regulatory Compliance

Certificate of Conformance:  
[View](#)

## Product Details

- Block and Transmit Desired Key VIS and NIR Spectral Bands with One Filter
- Remove The Need for Dual Sensor Setups
- Anti-Reflection Coating for Durability and Performance
- Various Mounting Thread Options Available

Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to ≥90% transmission in the visible (VIS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.

**Note:** Other filter threads are available upon request.