


Glan-Thompson Polarizer 350 - 2200nm, 8mm



Glan-Thompson Polarizer

Stock **#89-544** [CONTACT US](#)

- 1 +

A\$1,118.40

ADD TO CART

Qty 1-5
A\$1,118.40
Qty 6+
A\$1,064.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): 8.0
Coating: Single Layer MgF ₂
Diameter (mm): 25.40
Extinction Ratio:

<5 x 10 ⁻⁵
Substrate: Calcite
Length (mm): 28.00
Surface Quality: 20-10
Type: Linear Polarizer
Construction: Crystalline Glan-Thompson Polarizer
Transmitted Wavefront, P-V: λ/2 @ 632.8nm
Beam Deviation (arcmin): <3
Transmitted Wavefront Distortion (RMS): λ/4 @ 632.8 nm
Wavelength Range (nm): 350 - 2200
Damage Threshold, By Design: 1 J/cm² @ 1064nm, 10ns, 10Hz

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant