

Effilux 50 x 50 Lines, 50µm Matrix Mask



Effilux EFFI-Lase Structured LED Lighting Projector

Stock **#22-129** **1 In Stock**

-

1

+

A\$536⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$536.00 each
Need More?	Request Quote

Product Downloads

General	
Model Number:	EFFO-MSK-G04
Note:	50x50 lines pattern Pattern total size (on the mask) = 13mm x 13mm Line thickness (on the mask) = 50µm Step between each line center (on the mask) = 255µm
Manufacturer:	Effilux
Hardware & Interface Connectivity	

Power Supply:	
Power Supply Required and Sold Separately.	
USA: #15-874	
Europe: #15-875	
Japan: #73-409	
Korea: #73-409	
China: #15-874	

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- High Accuracy Without Speckle
 - Wide Range of Standard Masks Available
 - White, Blue, Red, and IR Colors Available
 - Compatible with [C Series Fixed Focal Length Lenses](#) and [HP Series Fixed Focal Length Lenses](#) for Pattern Projection
- Effilux EFFI-Lase Structured LED Lighting Projectors produce accurate, intense, and uniform lines, matrices, crosses, and arrays of points. Featuring an integrated driver board and easily interchangeable masks, these projectors are ready for plug and play use. Passive cooling and a temperature protection system ensure stable operation and help to prevent damage for long term operation. Effilux EFFI-Lase Structured LED Lighting Projectors offer the accuracy, power, and homogeneity of a laser projector without the speckle. These projectors are ideal for a range of machine vision applications such as 3D reconstruction, stereovision, and alignment.
- Note:** Masks sold separately, see accessories tab for options. Designed for use with a C-mount lens for pattern projection. 1.1" sensor lenses are recommended for masks with rectangular patterns to reduce distortion while 2/3" sensor lenses are sufficient for all other applications.